



PRISMATIC TIP DISCLAIMER

Congratulations on your new Fast Intentions exhaust system, equipped with our Prismatic (Tri Color) exhaust tips. These tips are put through a special coating process called PVD (Physical Vapor Deposition).

ONLY clean the exhaust tips with soap and water. ANY ammonia based glass cleaners, quick detailers containing wax, and/or hand wax can lead to discoloration and/or spot removal of the PVD coating.

Drying Process- Use a soft microfiber or cotton towel. Anything more abrasive could create scratches in the tips.

Heat Discoloration- These tips are dual wall, 304 Stainless Steel. The inside beauty ring (where the exhaust soot congregates) bares the most amount of exhaust heat. You may notice over time that this inside beauty ring may discolor/fade. It is completely normal as our standard Polished Stainless Steel tips turn gold on this same inside beauty ring.

Questions, Comments, Concerns, Contact Us:

By Email: info@fastintentions.com

By Telephone: (805) 522-3278